## **Product parameters**

Lens diameter:

3.9MM/5.5MM/8MM

Sensor:

CMOS

Resolution:

1920\*1080 1600\*1200

1280\*720 640\*480

Working temperature: 0-45 degrees

Battery:

2600mAh lithium battery

Power input:

DC 5V 500 mAh / 1A

Waterproof:

IP67 5-500cm

Focal length : Frame rate :

Frame rate: 30FPS
Wifi signal transmission range: 10 meters (accessible)

## How to use with phones 1.Download & Install APP

a.iOS device - download the app in the Apple Store or scan the QR code below and install it






YF LOOK

b.Android device - then googleplay download app or scan the QR code below, then install



## 2.Connection & use

- a. Turn on WiFi endoscope
- b. Use your mobile phone to search for the WiFi signal "YF LOOK..." and connect it (no password required).
- c. Open the app and you will see the real-time image.



- 1 Photos&Video
- 2 Take photo
- 3 Record Video
- 4 Resolution Setting
- 5 Split screens (split screen images and photo albums for easy comparison with previously stored images)
- 6 Image Rotating
- 7 screen brightness adjustment

## Charging

- 1. Please charge the equipment with 5v 1A USB charger.
- When charging, there are 4 pcs white LED power indicator lights, each one can represent 25% of the power. When all four battery indicator lights are on, it indicates that the charging is completed.
- 3. It is a built-in 2600 mAh lithium battery.

F€ (€ 🐧 🖾 🖫 Made in china